

## AMERICAS

### ARGENTINA

Piab Argentina S.A.  
25 de Mayo 1807  
San Martín  
AR-1650 BUENOS AIRES  
Phone: +54 11 4713 8550  
Fax: +54 11 4713 8552  
Email: info-argentina@piab.com

### BRAZIL

Regional office South America  
Piab do Brasil Ltda.  
R. Capitão Joaquim da Silva Rocha, 50  
Jardim Ana Maria  
BR-13208-750 JUNDIAÍ – SP  
Phone: +55 11 4492 9050  
Fax: +55 11 4522 4066  
Email: info-brasil@piab.com

### MEXICO

Piab Mexico & Central América  
65 Sharp Street  
HINGHAM MA US 02043  
Phone: +1 781 337 7309  
Fax: +1 781 337 6864  
Email: info-mxca@piab.com

### USA/CANADA

Regional office North America  
Piab USA, Inc.  
65 Sharp Street  
HINGHAM MA 02043 US  
Phone: +1 781 337 7309  
Fax: +1 781 337 6864  
Email: info-usa@piab.com

## ASIA

### CHINA

Piab (Shanghai) Co., Ltd  
Unit 401, B1k B1, No. 6000 Shenzhuan Rd  
Songjiang District  
CN-201619 SHANGHAI  
Phone: +86 21 5237 6545  
Fax: +86 21 5237 6549  
Email: info-china@piab.com

### INDIA

Piab Vacuum Technology Pvt. Ltd  
Plot no 11/C8, 11th block,  
Mugappair East,  
IN-600 037 CHENNAI  
Phone: +91 9444 25 36 48  
Email: info-india@piab.com

## JAPAN

Piab Japan Ltd.  
8-43-17 Tateishi Katsushika-ku,  
JP-124-0012 TOKYO  
Phone: +81 3 6662 8118  
Fax: +81 3 6662 8128  
Email: info-japan@piab.com

## SINGAPORE

Regional office Asia Pacific  
Piab Asia Pte Ltd  
4008 Ang Mo Kio Ave 10  
03-16 Techplace 1  
SG-569625 SINGAPORE  
Phone: +65 6455 7006  
Fax: +65 6455 0081  
Email: info-singapore@piab.com

## SOUTH KOREA

Piab Korea Ltd  
C-1906 Daelim Acrotel  
KR-Kangnam-Gu 467-6  
DOKOK-DONG  
Phone: +82 2 3463 0751  
Fax: +82 2 3463 0754  
Email: info-korea@piab.com

## EUROPE

### FRANCE

Piab  
Parc d'entreprises L'Esplanade  
10 rue Enrico Fermi  
Saint-Thibault des Vignes  
FR-77462 LAGNY SUR MARNE Cedex  
Phone: +33 1 6430 8267  
Fax: +33 1 6430 8285  
Email: info-france@piab.com

### GERMANY

Regional office Europe  
Piab Vakuum GmbH  
Otto-Hahn-Str. 14  
DE-35510 BUTZBACH  
Phone: +49 6033 7960 – 0  
Fax: +49 6033 7960 – 199  
Email: info-germany@piab.com

## GREAT BRITAIN

Piab Ltd.  
Vacuum Innovation House  
Station Road  
GB-LE12 6LQ EAST LEAKE  
Phone: +44 1509 857 010  
Fax: +44 1509 857 011  
Email: info-uk@piab.com

## ITALY

Piab ITALIA Srl  
Via Cuniberti, 58  
IT-10151 TORINO  
Phone: +39 011 226 36 66  
Fax: +39 011 226 21 11  
Email: info-italy@piab.com

## POLAND

Piab Polska Sp. z o.o.  
Ul. Astronomow 1  
PL-80-299 GDANSK  
Phone: +48 58 785 08 50  
Fax: +48 58 785 08 51  
Email: info-poland@piab.com

## SPAIN

Vacío Piab, S.L.  
Avda. Pineda, 2  
CASTELLDEFELS  
ES-08860 BARCELONA  
Phone: +34 93 6333876  
Fax: +34 93 6380848  
Email: info-spain@piab.com

## SWEDEN

Head office  
Piab AB  
Box 4501  
SE-183 04 TÄBY  
Phone: +46 8 630 25 00  
Fax: +46 8 630 26 90  
Email: info-sweden@piab.com

## SWITZERLAND

Piab Vakuum AG  
Stückirain 1  
CH-3266 WILER BEI SEEDORF  
Phone: +41 32 391 21 10  
Fax: +41 32 391 21 11  
Email: info-ch@piab.com

# piINLINE®

Eco-friendly energy saving  
inline vacuum ejector



No need to compromise

[www.piab.com](http://www.piab.com)



Art. No. 0123973GB, Rev.3  
Piab AB, 2012-11 / Printed in Sweden by Elanders




 **piab**

# piINLINE® Piab's eco-friendly energy saving inline vacuum ejector

Introducing piINLINE® a range of eco-friendly vacuum inline ejectors based on Piab's energy efficient COAX® technology.

- ▶ Superior vacuum performance even at low or fluctuating feed pressures.
- ▶ Dirt tolerant and durable design.
- ▶ Easy to retrofit existing energy wasting inline vacuum ejectors thanks to generic "plug-and-play" design.
- ▶ Easy and simple installation with push in connections - low installation cost.
- ▶ Installs directly on the hose near the suction point.
- ▶ Eliminates flow losses and enhances the vacuum performance.



Technical Information								Ordering Information							
piINLINE® vacuum ejector	Area of application	Dirt tolerant design	Optimum feed pressure	Air Consumption	Max vacuum	Max vacuum flow	Evacuation time, -50 kPa	Connections for compressed air and vacuum				Accessories			
			MPa	NI/min	-kPa	NI/min	s/l	4-4 mm	6-6 mm	8-8 mm	8-12 mm	Snap in mounting	Silencer	Snap in mounting for Silencer	
	MICRO Si	Leaking applications	0.6	7.2	75	16.8	4.9		0122882	-	-	5xMICRO 0123093	-	-	
	MICRO Bi	Low or fluctuating compressed air	0.18	8.4	83	13.8	10	0122880	0122883	-	-				
	MICRO Ti	Sealed applications	0.4	16.2	84	19.2	3.1		0122022						
		Leaking applications	x	0.6	22.2	75	18.6	2.6							
MICRO Xi	Sealed applications		0.5	7.8	92	14.4	7.3	0122881	0122884	-	-				
	MINI Si	Leaking applications	x	0.6	26.4	75	41.4	1.4	-	0122025	0122896	-	4xMINI 0123094	0125466	1xMINI 0126009
	MINI Pi	Low or fluctuating compressed air	x	0.314	26.4	90	34.2	1.8	-	0122894	0122897	-			
	MINI Xi	Sealed applications	x	0.5	27.6	94	37.2	1.6	-	0122895	0122898	-			
	MIDI Si	Leaking applications	x	0.6	105	75	186	0.40	-	-		0122032	1xMIDI 0123095	0123031	1xMIDI 0123096
	MIDI Pi	Low or fluctuating compressed air	x	0.3	120	90	162	0.48	-	-	-	0122899			
	MIDI Xi	Sealed applications	x	0.45	110	95	168	0.44	-	-	-	0122900			

Leaking applications include handling porous materials such as corrugated board. Sealed applications include handling electronics, plastic parts and other non-porous materials.

